CONDENSER			TNI	- GWOID CO	· C	OWG. # CW4C141412-DRB-ST	REV -
ATC-792E SCALE N	TS	EVAPCO,	INC.	Evast	S	SERIAL #	DATE: 11/3/2025
NOTES 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CASING SECT 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWI 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT US FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFE RECOMMENDED STEEL SUPPORT DRAW 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]	NGS) SE R TO			FACE B PLAN VIEW	ACCES	FACE C (M) ACCESS DOOR SS DOOR (M) EACE A	FACE D
1'-9 3/8" [543] 3'-6	73]	1'-10 7/8" * [581]			1'-2" [355]	FACE A	
(M)		2'-11 3/8" [899]		1	Acc	CESS COOR COOR COOR COOR COOR COOR COOR CO	
3'-6" [1067] * O REFRIG IN REFRIG OUT O	O O REFRIG IN	5'-11 3/8" [1813]	4393]				
1'-11 1/8" [587]		_5 1/4" [133] * 5'-6 1/4" [1683]					
3" [76] 2'-0 3/8" [619] 6'-10 7/8" [2105] 6'-11 3/4" [2127] 7'-4"	(2) 2" [50] MPT MAKE-UP (2) 2" [50] MPT DRAIN	1'-3" [381] (2) 3" [80] MPT OVERFLOW		1'-5 1/ [435 _]	8"	13'-11 3/4" [4261]	
[2235] 15'-1 [460 FACE SHIPPING WEIGHT 31160 lbs+ [14135] kg+	[130] /8" 1] B	33180 lbs+ [15055] kg+	HEAVIEST SECTIO WEIGHT	N 42200 lba	:+ [6075] kg+	FACE A NO. OF SHIPPING SECTIONS 4	DRAWN BY: JLG