UNIT	COOLING TOWER		
MODEL #	AT 424-4P40	SCALE NTS	

EVAPCO, INC. Evapeo

OWG. #	T3244048-DRC-ST	REV.
SERIAL #		DATE 11/5/2025

NOTES:

SHIPPING


WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
- 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]




HEAVIEST SECTION

WEIGHT



FACE A




55720 lbs+ [25275] kg+

OPERATING

WEIGHT

96920 lbs+ [43965] kg+



9430 lbs+ [4280] kg+

NO. OF SHIPPING SECTIONS