NIT	COOLING TOW	ER		TNIC			T4284824-DRA-ST	REV.
ODEL #	AT 428-2O48	SCALE NTS	EVAPCO	, INC.		SERIAL #		DATE 11/4/2025
2. HÉAVII 3. MPT D FPT DE BFW D GVD D FLG DE 4. +UNIT ACCES 5. MAKE- 20 psi 1 6. 3/4" [18 REFEE DRAW 7. DIMEN [ME 8. PAN FI EVAPC BY OTI 9. PAN E6	SIONS LISTED AS FOLLO GLISH FT-IN :TRIC] [mm] .UME BOX EQUALIZERS : :O. PAN EQUALIZER PIPII	EAD HREAD WELDING LUDE RY DRAWINGS) [344 kPa] LES. EEL SUPPORT DWS: SUPPLIED BY NG IS SUPPLIED	PLAN	FACE B		ACE C	(4) ACCESS DOOR	FACE D
			7" [178]	1'-5 1/4" [438]				
2" [51] ——	(4) 14" [350] BFW/GVD OUTLET (4) 4" [100] MPT OVERFLOW	11'-6" [3505] — 13'-1 1/4" [3994]	9'-2 1/4" [2800] 17'-5 1/2" [5321] 8'-3 1/4" [2521] 8'-3 1/4" [2521]	11'-3 3/4"	11'-10 1/2"	G B G S	4) 12" [300] FW/GVD EQUALIZER SEE NOTE #9)	
	(4) 3" [80] MPT — MAKE-UP (4) 4" [100] MPT — DRAIN		9" [229] 4" [102]	1 1/2" [38]		3'-7' [1092 51'-1" 15570]		1 1/2" [38] DRAWN BY: MER