UNIT	COOLING TOW	/ER	F\/ADC	EVAPCO, INC. evapco		DWG. # CT4C071824-D	RA-ST REV
MODEL #	AT 17-2l18	SCALE NTS	T EVAPC	O, INC.		SERIAL #	DATE 11/13/2025
2. HEAVIES 3. MPT DEI FPT DEN BFW DE GVD DE FLG DEN 4. +UNIT W ACCESS 5. 3/4" [19M REFER T SUPPOF 6. DIMENS ENGL [METI 7. MAKE-U	I MOTOR LOCATION ST SECTION IS FAN/CAS NOTES MALE PIPE THR NOTES FEMALE PIPE TH NOTES BEVELED FOR IN NOTES FLANGE /EIGHT DOES NOT INCL SORIES (SEE ACCESSOI MM] DIA. MOUNTING HOI TO RECOMMENDED STE TORAWING IONS LISTED AS FOLLO LISH FT-IN RIC] [mm] P WATER PRESSURE IN [137 KPa], 50 psi MAX	EAD HREAD WELDING  .UDE RY DRAWINGS) LES. EEL DWS:		FACE B PLAN VIEW	ACCESS I	FACE C DOOR FACE A	ACCESS DOOR  FACE D
			1'-2" [ 356 ]				
1'- ( )	9 3/8" 543 ]	3'-8"		2'-11 3/8" [ 899 ] 4'-5 1/8" [ 1349 ]			
	8" [200]		1	[ 1349 ] 2'-4 3/4"			
	8" [200] BFW/GVD INLET		2" [50] MPT	5'-1/4" [ 1530 ]			
	3" [80] M OVERFLC 8" [7 BFW/ OUT		4 1/4"		-		
	-	7'-4" [ 2235 ] <b>FACE B</b>			-	- 18'-0" [ 5486 ] <b>FACE A</b>	-
SHIPPING WEIGHT	7570 lbs+ [3-	435] kg+	OPERATING WEIGHT 12700 lbs+ [5765] I	rg+ HEAVIEST SECTION WEIGHT	ON 4940 lbs+ [2245] kg+	NO. OF SHIPPING SECTIONS	2 DRAWN BY: MBG