ODEL#			EVAPCO, INC. evapco		T4284836-DRA-ST	REV.
A-	T 428-3O48	SCALE NTS	EVAPCO, IN		SERIAL #	DATE 11/4/2025
3. MPT DENOTE FPT DENOTE BFW DENOTE GVD DENOTE PE DENOTES 4. +UNIT WEIGH ACCESSORIE 5. MAKE-UP WA 20 psi MIN [13 6. 3/4" [19MM] D RECOMENDE 7. DIMENSIONS ENGLISI [METRIC 8. PAN FLUME E EVAPCO. PAI BY OTHERS.	ECTION IS UPPER S ES MALE PIPE THRE ES FEMALE PIPE THRE ES BEVELED FOR W ES GROOVED ES FLANGE ES PLAIN END HT DOES NOT INCLU ES (SEE ACCESSOR ATER PRESSURE ED AND HAX [ED STEEL SUPPORT ELISTED AS FOLLOW H FT-IN C] MM ED OX EQUALIZERS S N EQUALIZER PIPIN ESTER NIPPLE IS 11'-1'	EAD READ READ //ELDING JDE Y DRAWINGS) 344 kPa] ES. REFER TO DRAWING. VS: UPPLIED BY G IS SUPPLIED	FACE B PLAN VIEW		CE C (4) ACCESS DOOR	FACE D
			7" [178] 1'-5 1/4" [438]		<u>CE A</u>	
			438			
			10'-2 1/4" [3105]			
[51]			2" [51] 18'-5 1/2" [5626]	11'-10 1/2" (4) 14" [350] BFW/GVD INLET		
			8'-3 1/4" [3753] [2521]			
(4	(4) 14" [350] -	11'-6" [3505]	2'-2" [660] 1'-5 3/8" [441]	9 1/8"	(4) 12" [300] BFW/GVD EQUALIZER (SEE NOTE #9)	
(4	(4) 3" [80] MPT —/ MAKE-UP 4) 4" [100] MPT — DRAIN	13'-5 1/2"	9" [229]	1 3/8" [35] (TYP)	-	
		13'-6 1/2"		23'-9"	3'-7" [1092]	
	5 1/8" — - [130] — 28'-3 !	13'-11 1/4" [4248]	1 1/2" —		1'-1" 5570]	1 1/2" [38]
-	28'-3 ! [862 FACE				CE A	
HIPPING		OPERA		AVIEST SECTION 12210 lbs+ [5540] kg+	NO. OF SHIPPING SECTIONS	DRAWN BY: MER