NIT	COOLING TOW	ER	EVAPCO, INC. Evapco		DWG. # T4284836-DRA-ST	REV.
ODEL #	AT 428-3P48	SCALE NTS	EVAPCO, IN		SERIAL #	DATE 11/3/2025
2. HEAVIE 3. MPT DI FPT DE BFW D GVD DI FLG DE PE DE 4. +UNIT ACCES 5. MAKE-I 20 psi N RECON 7. DIMEN E [N 8. PAN FL EVAPC BY OTF 9. PAN EC	IN MOTOR LOCATION EST SECTION IS UPPER S ENOTES MALE PIPE THR ENOTES FEMALE PIPE THE ENOTES BEVELED FOR V ENOTES GROOVED ENOTES PLAIN END WEIGHT DOES NOT INCLE SORIES (SEE ACCESSOF UP WATER PRESSURE MIN [137 KPa], 50 psi MAX MM] DIA. MOUNTING HOI MENDED STEEL SUPPOR SIONS LISTED AS FOLLO NGLISH FT-IN METRIC] MM LUME BOX EQUALIZERS S IO. PAN EQUALIZER S IO. PAN EQUALIZER S ACH STEP SIDE.	EAD IREAD WELDING UDE RY DRAWINGS) [344 kPa] LES. REFER TO T DRAWING. WS: SUPPLIED BY NG IS SUPPLIED	FACE B PLAN VIEW		CE C (4) ACCESS DOOR	FACE D
			711	<u>FA</u>	CE A	
			7" 1'-5 1/4" [438]			
2" [51] -			10'-2 1/4" [3105] 2"	11'-10 1/2" (4) 14" [350] BFW/GVD INLET	00 00	
	0/6		8'-3 1/4" [3753]			,
	(4) 14" [350] -/ // BBW/GVD OUTLET (4) 4" [100] MPT -/ OVERFLOW (4) 3" [80] MPT -/ MAKELID	11'-6" [3505]	2'-2" [660] 1'-5 3/8" [441]	9 1/8" [232]	(4) 12" [300] BFW/GVD EQUALIZER (SEE NOTE #9)	
	(4) 3" [80] MPT / MAKE-UP (4) 4" [100] MPT / DRAIN	13'-5 1/2" [4102] 13'-6 1/2" [4128]		1 3/8" [35] (TYP)	3'-7" [1092]	
	5 1/8" —— - [130] —— - 28'-3	13'-11 1/4" [4248]	1 1/2" [38]		1'-1" 5570]	1 1/2" [38]
ļ	28'-3 5/8" [8626] FACE B			<u>FA</u>	CE A	
SHIPPING WEIGHT	72400 lbs+ [32	2845] kg+ OPERA WEIG	TING 137080 lbs+ [62180] kg+ HEA	VIEST SECTION 12380 lbs+ [5620] kg+	NO. OF SHIPPING SECTIONS 8	DRAWN BY: MER