COOLING TOWER		FVADCO TI	lo evanço	DWG.# CT4C141436-DRA-ST	REV -
AT 214-3I14	SCALE NTS	EVAPCO, I	VC.	SERIAL#	DATE: 11/21/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CASI 3. MPT DENOTES MALE PIPE THRE FPT DENOTES FEMALE PIPE THR BFW DENOTES BEVELED FOR W GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLU ACCESSORIES (SEE ACCESSOR' 5. 3/4" [19MM] DIA. MOUNTING HOLE REFER TO RECOMMENDED STEE SUPPORT DRAWING 6. DIMENSIONS LISTED AS FOLLOW ENGLISH FT-IN [METRIC] [mm] 7. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [3	AD EAD ELDING DE / DRAWINGS) ES. EL		FACE B PLAN VIEW	FACE C (M) ACCESS DOOR ACCESS DOOR (M)	FACE D
1'-9 3/8" [543]		1'-2" [355]	A	FACE A	
(M)		3'-8"	2'-11 3/8" [898]	ACCESS DOOR ACCESS DOOR (M)	
			5'-5 1/8" [1654]	- 2" [51]	
(2) 8" [200] — BFW/GVD INLET		9'-9 5/8" [2988]	5'-6 1/4" [1683]		
(2) 3" [80] MPT OVERFLOW	[1	2 1/4" 276] -1'-2 7/8" [378]			
(2) 2" [50] MPT (2) 8" [200] - BFW/GVD OUTLET (2) 3" [80] MI DRA	[2105] PT 6'-11 3/ [2127]	15]	1 3/8" [35] - 	13'-11 3/4" [4261]	
	FACE B			FACE A	
SHIPPING WEIGHT 11500 lbs+ [5220] kg	+ OPERATING WEIGHT	19350 lbs+ [8780] kg+	EAVIEST SECTION 3790 lbs+ [1720 WEIGHT] kg+ NO. OF SHIPPING SECTIONS 4	DRAWN BY: JLG