

UNIT		COOLING TOWER		<div>EVAPCO, INC.</div> <div><div>evapco</div></div>	DWG. #	T3041224-DRJ-ST	REV.	-											
MODEL #		AT 14-2G12			SCALE	NTS		SERIAL #	DATE	8/25/2025									
<div>NOTES:</div> <div>1. (M)- FAN MOTOR LOCATION</div> <div>2. HEAVIEST SECTION IS UPPER SECTION</div> <div>3. MPT DENOTES MALE PIPE THREAD</div> <div>  FPT DENOTES FEMALE PIPE THREAD</div> <div>  BFW DENOTES BEVELED FOR WELDING</div> <div>  GVD DENOTES GROOVED</div> <div>  FLG DENOTES FLANGE</div> <div>4. +UNIT WEIGHT DOES NOT INCLUDE</div> <div>  ACCESSORIES (SEE ACCESSORY DRAWINGS)</div> <div>5. MAKE-UP WATER PRESSURE</div> <div>  20 psi MIN [137 kPa], 50 psi MAX [344 kPa]</div> <div>6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO</div> <div>  RECOMENDED STEEL SUPPORT DRAWING.</div> <div>7. DIMENSIONS LISTED AS FOLLOWS:</div> <div>  ENGLISH FT-IN</div> <div>  [METRIC] [mm]</div>																			
<div>FACE B</div> <div>PLAN VIEW</div>					<div>FACE C</div> <div><div><div>ACCESS DOOR</div><div>ACCESS DOOR</div></div><div><div>4'-5 3/4" [ 1365 ]</div></div></div>														
<div>FACE B</div> <div><div><div>1'-3/4" [ 324 ]</div><div>2'-1/8" [ 613 ]</div><div>6" [150] MPT INLET</div><div>6" [150] MPT OUTLET</div><div>1" [25] MPT MAKE-UP</div><div>5 7/8" [ 149 ]</div><div>2" [50] MPT OVERFLOW</div><div>2" [50] MPT DRAIN</div><div>3'-1 1/2" [ 953 ]</div><div>1'-7 3/4" [ 502 ]</div><div>10 1/4" [ 260 ]</div><div>2'-1/4" [ 616 ]</div><div>4'-1/2" [ 1232 ]</div><div>4 3/8" [ 111 ]</div><div>5 1/8" [ 130 ]</div><div>3" [ 76 ]</div><div>1'-1" [ 330 ]</div></div></div>					<div>FACE D</div> <div><div><div>1'-1" [ 330 ]</div><div>3 1/8" [ 79 ]</div><div>6'-3" [ 1905 ]</div><div>11'-11 3/4" [ 3651 ]</div></div></div>														
<div>FACE A</div>					<div>FACE A</div>														
SHIPPING WEIGHT		2570 lbs+ [1170] kg+		OPERATING WEIGHT		4690 lbs+ [2130] kg+		HEAVIEST SECTION WEIGHT		1810 lbs+ [825] kg+		NO. OF SHIPPING SECTIONS		2		DRAWN BY:		KWC	