UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 4-4F6

EVAPCO, INC. Evapeo



DWG. # REV. WB3040608-DRE-ST DATE_{12/14/2025} SERIAL #

NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN METRIC [mm]





FACE C

FACE B PLAN VIEW



FACE A





DRAWN BY: NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 3150 lbs+ [1430] kg+ 4800 lbs+ [2180] kg+ 2640 lbs+ [1200] kg+ WEIGHT WEIGHT WEIGHT