UNIT	CLOSED CIRCUIT COOLER	
MODEL #	ATWB 4-4F9	SCALE NTS

EVAPCO, INC. Evapeo



DWG. # REV. WB3040908-DRE-ST DATE 11/4/2025 SERIAL #


NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN METRIC [mm]

FACE C


4'-5 3/4' [1365] **PLAN VIEW**




FACE D

DRAWN BY:

FACE A





NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 4660 lbs+ [2115] kg+ 7050 lbs+ [3200] kg+ 3990 lbs+ [1810] kg+ WEIGHT WEIGHT WEIGHT