



| | | | | |
|------------------------|--------------|--|---------------------------|------------------|
| UNIT COOLING TOWER | | <div>EVAPCO, INC.</div>  | DWG. # T3121424-DRE-ST | REV. - |
| MODEL # AT 112-2L14 | SCALE NTS | | SERIAL # | DATE 8/7/2025 |


NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 3/4" [19MM] DIA. MOUNTING HOLES.
REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]

FACE B



FACE A



| | | | | | | | | |
|-----------------|----------------------|------------------|-----------------------|-------------------------|----------------------|--------------------------|---|---------------|
| SHIPPING WEIGHT | 8420 lbs+ [3820] kg+ | OPERATING WEIGHT | 15750 lbs+ [7145] kg+ | HEAVIEST SECTION WEIGHT | 5550 lbs+ [2520] kg+ | NO. OF SHIPPING SECTIONS | 2 | DRAWN BY: KDS |
|-----------------|----------------------|------------------|-----------------------|-------------------------|----------------------|--------------------------|---|---------------|