



UNIT	COOLING TOWER		<b>EVAPCO, INC.</b> 	DWG. #	T4282424-DRA-ST	REV.
MODEL #	AT 228-2L24	SCALE NTS		SERIAL #		DATE 2/20/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. 3/4" [19MM] DIA. MOUNTING HOLES.  
REFER TO RECOMMENDED STEEL SUPPORT  
DRAWING
7. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]



## FACE B



## FACE A

SHIPPING WEIGHT 32420 lbs+ [14710] kg+ OPERATING WEIGHT 65060 lbs+ [29515] kg+ HEAVIEST SECTION WEIGHT 10650 lbs+ [4835] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: MER