


UNIT	CLOSED CIRCUIT COOLER		EVAPCO, INC.  [®]		DWG. #	WB3091114-DRC-ST	REV.
MODEL #	ATWB 9-7L11	SCALE NTS	SERIAL #		DATE 1/11/2026		

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. *APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN
METRIC [mm]



FACE B



evapco


DWG. #

WB309114-DRC-ST

REV.

SERIAL #

DATE 1/11/2026



FACE A

SHIPPING WEIGHT 15480 lbs+ [7025] kg+ OPERATING WEIGHT 22120 lbs+ [10035] kg+ HEAVIEST SECTION WEIGHT 13840 lbs+ [6280] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: SLR