


UNIT	CLOSED CIRCUIT COOLER		<b>EVAPCO, INC.</b> 	DWG. #	WB3091212-DRC-ST	REV.
MODEL #	ATWB 9-6L12	SCALE NTS		SERIAL #		DATE 1/12/2026


NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. \*APPROXIMATE DIMENSIONS DO NOT USE  
FOR PRE-FABRICATION OF CONNECTING  
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN  
METRIC [mm]



### FACE B



t 565

SHIPPING WEIGHT 14960 lbs+ [6790] kg+ OPERATING WEIGHT 22080 lbs+ [10020] kg+ HEAVIEST SECTION WEIGHT 13160 lbs+ [5970] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: SLR