UNIT COOLING TOWER			EV/A DO	EVAPCO, INC. evapco			-DRA-ST REV
MODEL #	AT 17-2J18	SCALE NTS	EVAPCO), INC.		SERIAL #	DATE _{11/13/2025}
2. HEAVIE 3. MPT DI FPT DE BFW D GVD DI FLG DE 4. +UNIT ACCES 5. 3/4" [19 REFER SUPPO 6. DIMEN: ENG [ME' 7. MAKE-I	IN MOTOR LOCATION EST SECTION IS FAN/CASII ENOTES MALE PIPE THRE, ENOTES FEMALE PIPE THRE, ENOTES BEVELED FOR W ENOTES GROOVED ENOTES FLANGE WEIGHT DOES NOT INCLU SSORIES (SEE ACCESSOR) MMJ DIA. MOUNTING HOLE TO RECOMMENDED STEED ORT DRAWING SIONS LISTED AS FOLLOW GLISH FT-IN TRIC] [mm] UP WATER PRESSURE MIN [137 KPa], 50 psi MAX [3	AD READ ELDING JDE Y DRAWINGS) ES. EL		FACE B PLAN VIEW	ACCESS D	FACE C OOR FACE A	ACCESS DOOR FACE D
			1'-2" [356]				
1	'-9 3/8" [543]	3'-8"		2'-11 3/8" [899] 4'-5 1/8" [1349]			
	8" [200] BFW/GVD INLET		211 FE01 MDT	2'-4 3/4" 3778]	-		
			2" [50] MPT 8'-3 3/4" [2532]	5'-1/4" (1530]			
	3" [80] MPT OVERFLOW 8" [20 BFW/GV OUTLE	00] 00/00 3'-1 3/4 [959]	4 1/4"	1 3/8" [35]	-		
		7'-4" [2235] FACE B	- -		ļ-	18'-0" [5486] FACE A	-
					-		
SHIPPING WEIGHT	7710 lbs+ [350	00] kg+	OPERATING 12840 lbs+ [5825] k	g+ HEAVIEST SECTION WEIGHT	ON 5080 lbs+ [2305] kg+	NO. OF SHIPPING SECTION	DRAWN BY: MBG