UNIT	CLOSED CIRCUIT	CUIT COOLER	
MODEL #	ATWB 12-7N20	SCALE NTS	
NOTES:	N MOTOR LOCATION		




DWG. # REV. WB3122014-DRC-ST DATE_{11/21/2025} SERIAL #

FACE D


- 2. HEAVIEST SECTION IS UPPER SECTION
 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]


FACE C





FACE A





DRAWN BY: SLR NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 34100 lbs+ [15470] kg+ 38610 lbs+ [17515] kg+ 58550 lbs+ [26560] kg+ WEIGHT WEIGHT WEIGHT