UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 24-7P40

EVAPCO, INC. Evapeo



DWG. # REV. WB3244014-DRC-ST DATE 11/5/2025 SERIAL #


NO. OF SHIPPING SECTIONS


## NOTES:

**SHIPPING** 

WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]





235320 lbs+ [106740] kg+

HEAVIEST SECTION

WEIGHT

34310 lbs+ [15565] kg+

**OPERATING** 

WEIGHT

155380 lbs+ [70480] kg+