UNIT CLOSED CIRCUIT COOLER			EVAPCO, INC. evapco			DWG. # WB3122008-DRC-SF REV	
ODEL #	ATWB 12-4M20-Z	SCALE NTS	EVAPCO	, INC.		SERIAL #	DATE 11/21/2025
2. HÉAVIE B. MPT DE FPT DEI BFW DEI GVD DE FLG DEI PE DEN I. + UNIT \ ACCES FOR AG 5. * - APPF FOR PR PIPING 7. SERIES DRAIN E 3. 3/4" [191	N MOTOR LOCATION ST SECTION IS UPPER SE NOTES MALE PIPE THREA NOTES FEMALE PIPE THR ENOTES BEVELED FOR WE NOTES GROOVED NOTES FLANGE OTES PLAIN END WEIGHT DOES NOT INCLU SORIES (SEE SEPARATE I CCESSORIES) JP WATER PRESSURE IIN [137 kPa], 50 psi MAX [34 ROXIMATE DIMENSIONS DO IE-FABRICATION OF CONN FLOW PIPING AND AUX. C SMM] DIA. MOUNTING HOLE MENDED STEEL SUPPOR	AD IEAD ELDING JDE DRAWINGS 44 kPa] O NOT USE JECTING CROSSOVER ES. REFER TO	FAI PLAN VI	CE B EW	FACE	ACCESS DOOR	FACE D
	ENGLISHED AS FOLLOW ENGLISH FT-IN METRIC [mm]		7" [178]	1'-3 1/4" [387]	FACE A	<u>.</u>	
	(4) 4" [100] BFW — FLUID IN	5'-9 1/4" *	3'-3/8" * [924] 9'-1/8" [2748]	(4) 1/2" [15] FPT VENT			
	2'-6 3/4" *		- (4) 4" [100] BFW FLUID OUT 15'-2 3/8" [4632]	RIES FLOW PIPING	(G)A.		
	2" [50] MPT — MAKE-UP 2'-1 1/4" [643]		T	(SEE NOTE 7)			
	3 5/8" DRA	30] MPT AIN 3" [80] MPT OVERFLOW [133] 1/4" [108]	T.				
		7'-2" 2184] ————————————————————————————————————		2'-1/2" [622]	20'. [60'		
SHIPPING WEIGHT	26190 lbs+ [11	880] kg+ OPERAT		HEAVIEST SECTION WEIGHT	21680 lbs+ [9835] kg+	NO. OF SHIPPING SECTIONS	2 DRAWN BY: JLG