	ATWB 12-7O18-Z	CCALE			1 T T T T T T T T T T T T T T T T T T T	DWG. # WB3121814-DRC-SF SERIAL #	
1. (M) - FAN	ATWB 12-7O18-Z	SCALE NTS	EVAPCO,	INC. Eva	SERIAL #		
3. MPT DEN FPT DEN BFW DEN GVD DEN FLG DEN PE DENC 4. + UNIT W ACCESS FOR ACC 5. MAKE-UF 20 psi MII 6. * - APPRC FOR PRE PIPING 7. SERIES F 8. 3/4" [19M RECOMN	N MOTOR LOCATION ST SECTION IS UPPER SEC NOTES MALE PIPE THREA IOTES FEMALE PIPE THREA IOTES GROOVED NOTES GROOVED NOTES FLANGE DIES PLAIN END VEIGHT DOES NOT INCLUE SORIES (SEE SEPARATE D CESSORIES) P WATER PRESSURE N [137 KPa], 50 psi MAX [34 OXIMATE DIMENSIONS DO E-FABRICATION OF CONNE FLOW PIPING AND AUX. C Y OTHERS IM] DIA. MOUNTING HOLES MENDED STEEL SUPPORT IONS LISTED AS FOLLOWS	DEAD LDING DE RAWINGS 4 kPa] D NOT USE ECTING ROSSOVER 5. REFER TO DRAWING.		FACE B PLAN VIEW	FACE C ACCESS FACE A	DOOR FACE D	<u>)</u>
	ENGLISH FT-IN METRIC [mm]		[178]	1'-3 1/4" [387]	JC = = = = = = = = = = = = = = = = = = =	<u>-</u> 51	
	(4) 4" [100] BFW FLUID IN 3'-11 3/4" *	5'-9 1/4" *	3'-3/8" * [924] * 10'-5 1/8" [3180] (4) 4" [100] BFW FLUID OUT 16'-7 3/8" [5064]	SERIES FLOW PIPING (SEE NOTE 7)	[PD		
	2" [50] MPT MAKE-UP 2'-1 1/4" [643] 3 5/8"	[80] MPT AAIN OVERFLO	6" * 6'-2 1/4" [1884] APT DW	AUX. CROSSOVER DRAIN (SEE NOTE 7)			
	4 [5 1/4" [133] 1/4" 108] 7'-2" 2184] 11'-10" [3607] FACE B		1'-11 1/8"			