



UNIT		CLOSED CIRCUIT COOLER		EVAPCO, INC. 		DWG. # WB3243614-DRC-SF		REV. -									
MODEL # ATWB 24-7M36-Z		SCALE NTS				SERIAL #		DATE 12/16/2025									
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS. 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 9. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [MM]																	
 FACE B				 FACE A													
SHIPPING WEIGHT		138120 lbs+ [62655] kg+		OPERATING WEIGHT		209720 lbs+ [95130] kg+		HEAVIEST SECTION WEIGHT		30460 lbs+ [13820] kg+		NO. OF SHIPPING SECTIONS		6		DRAWN BY: JLG	