JNIT	CLOSED CIRCUIT C	OOLER
MODEL #	ATWB 24-5P40-Z	SCALE NTS

EVAPCO, INC. Evapco


DWG. # REV. WB3244010-DRC-SF DATE 11/8/2025 SERIAL #

NOTES:


SHIPPING

WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE
- FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [MM]



FACE A



190080 lbs+ [86220] kg+

HEAVIEST SECTION

WEIGHT

25730 lbs+ [11675] kg+

OPERATING

WEIGHT

121060 lbs+ [54915] kg+