UNIT	CLOSED CIRCUIT COOLER	
MODEL #	ATWB 24-4N14-Z	SCALE NTS

EVAPCO, INC. Evapco

WG. #	WB3241408-DRC-SF	REV.
ERIAL #		DATE <sub>11/10/2025</sub>

## NOTES:

**SHIPPING** 

WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
  FPT DENOTES FEMALE PIPE THREAD
  BFW DENOTES BEVELED FOR WELDING
  GVD DENOTES GROOVED
  FLG DENOTES FLANGE
  PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]




FACE B

HEAVIEST SECTION

WEIGHT


16040 lbs+ [7280] kg+



**FACE C** 

FACE D

DRAWN BY: JLG



60340 lbs+ [27370] kg+

OPERATING

WEIGHT

38200 lbs+ [17330] kg+

## FACE A 1'-3 1/4" [ 387 ] SERIES FLOW PIPING SEE NOTE 7 AUX. CROSSOVER DRAIN SEE NOTE 7 [ 470 ] 13'-11 3/4" [ 4261 ] FACE A

NO. OF SHIPPING SECTIONS