



UNIT CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. # WB3241812-DRC-SF	REV. -
MODEL # ATWB 24-6O18-Z	SCALE NTS		SERIAL #	DATE 6/20/2025

NOTES:


- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]

FACE B




FACE D


FACE A



FACE B



FACE A



SHIPPING WEIGHT 61260 lbs+ [27790] kg+	OPERATING WEIGHT 94500 lbs+ [42865] kg+	HEAVIEST SECTION WEIGHT 26710 lbs+ [12120] kg+	NO. OF SHIPPING SECTIONS 4	DRAWN BY: JLG
-------------------------------------------	--------------------------------------------	---------------------------------------------------	-------------------------------	------------------