UNIT **CLOSED CIRCUIT COOLER** MODEL # ATWB 20-6L12-Z NTS


EVAPCO, INC. Evapco

DWG. # REV. WB36M1212-DRC-SF DATE_{11/14/2025} SERIAL #


NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]





FACE A





SHIPPING 36400 lbs+ [16515] kg+ WEIGHT

OPERATING WEIGHT

55360 lbs+ [25115] kg+

HEAVIEST SECTION WEIGHT

15640 lbs+ [7095] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: SLR