JNIT	CLOSED CIRCUIT COOLER	
MODEL #	ATWB 24-6P36-Z	SCALE NTS

EVAPCO, INC. Evapco

DWG. # REV. WB3243612-DRC-SF DATE_{12/13/2025} SERIAL #

NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
 - PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE
- FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.

123920 lbs+ [56210] kg+


WEIGHT

WEIGHT

9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [MM]



26910 lbs+ [12210] kg+



WEIGHT

190600 lbs+ [86455] kg+