UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 20-4J12-Z


EVAPCO, INC. Evapea

DWG. # REV. WB36M1208-DRC-SF DATE 11/16/2025 SERIAL #


## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]





**FACE A** 





**SHIPPING** 28820 lbs+ [13075] kg+ WEIGHT

OPERATING WEIGHT

45160 lbs+ [20485] kg+

HEAVIEST SECTION WEIGHT

11850 lbs+ [5380] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: SLR