UNIT CLOSED CIRCUIT COOLER			EVAPCO, INC. Evapeo				wg. # CW4C071808-DRA-S	T REV
MODEL #	ATWB 7-4I18	SCALE NTS	EVAP	CO, II	NC.	SE	ERIAL #	DATE _{10/29/2025}
2. HÉAVIES 3. MPT DEI FPT DEN BFW DE GVD DEI FLG DEN PE DEN 4. +UNIT W ACCESS 5. MAKE-U 20 psi MI 6. *-APPRO FOR PRI PIPING 7. 3/4" [19m RECOMM	MOTOR LOCATION BT SECTION IS FAN/CASI NOTES MALE PIPE THRE IOTES FEMALE PIPE THRE IOTES FEMALE PIPE THR NOTES GROOVED NOTES FLANGE DTES PLAIN END FEIGHT DOES NOT INCLU- ORIES (SEE ACCESSOR P WATER PRESSURE N [137 kPa], 50 psi MAX [() XIMATE DIMENSIONS DC E-FABRICATION OF CON mm] DIA. MOUNTING HOL MENDED STEEL SUPPOR IONS LISTED AS FOLLOV ENGLISH FT-IN METRIC [mm]	AD READ FELDING JDE Y DRAWINGS) 344 KPa] D NOT USE NECTING ES. REFER TO RT DRAWING.		FACE PLAN VIE		ACCESS DOOR		FACE D
1'-9 3/8" - [543] - 2" [50] MF MAKE-U 2" [50] MF DRAI 1'-11 1 1' 587 1' 76	JP DT JB JB JB JB JB JB JB JB JB JB JB JB JB	FLUID IN FLUID OUT	2'-11 3/8" [899] 1'-10 7/8" * 4'-8 3/8" [1432] 12'-8" [3861] 5'-1/4" [1530] 1'-3" [381] 	(2) 1/2 FPT V				
		-4" 235]		1'-4 7/8" [429]	' 		8'-0" 5486]	
SHIPPING		<u>E B</u>	OPERATING 22120 lbc [1		HEAVIEST SECTION		NO. OF SHIPPING SECTIONS	DRAWN BY:
WEIGHT	16100 lbs+ [73	305] kg+	WEIGHT 22130 lbs+ [1	0040] kg+	WEIGHT	13080 lbs+ [5935] kg+	NO. OF SHIPPING SECTIONS 2	TAM