| INIT CLOSED CIRCUIT COOLER | | | 1 | | | DV DV | VG. # CIVIACOTO 40.6 D.D.A. GE | REV. | \neg |
|--|---|--|----------------------|--|------------------------------|---|--------------------------------|-------------------|------------|
| 10DEL # | | CONT | ⊢ E` | VAPCO, II | NC. Evapeo | SE | CW4C072406-DRA-SF | DATE 10/30/202 | |
| NOTES: 1. (M)- FAN 2. HEAVIE: 3. MPT DE FPT DEI BFW DE GVD DE FLE DEN 4. +UNIT W ACCESS 5. MAKE-U 20 psi M 6. *-APPRC PIPING 7. SERIES DRAIN E 8. 3/4" [19M 9. DIMENS EN | ATWB 7-3J24-Z N MOTOR LOCATION ST SECTION IS FAN/CASIN NOTES MALE PIPE THREA NOTES FEMALE PIPE THREA NOTES FEMALE PIPE THREA NOTES GROOVED NOTES FLANGE IOTES PLAIN END WEIGHT DOES NOT INCLUE SORIES (SEE ACCESSORY JIP WATER PRESSURE IIN [137 kPa], 50 psi MAX [34 OXIMATE DIMENSIONS DO RE-FABRICATION OF CONN STEOW PIPING AND AUX. OBY OTHERS. MMJ DIA. MOUNTING HOLE IMENDED STEEL SUPPORT SIONS LISTED AS FOLLOW NGLISH FT-IN ETRIC [mm] | NG SECTION AD LEAD ELDING DE (**DRAWINGS**) 44 kPa] NOT USE JECTING CROSSOVER ES. REFER TO T DRAWING. | | FACE B PLAN VIEW | ACCESS DOO | FACE C | ACCESS DOOR | FACE I | |
| (2) 2" [50] MAK (2) 2" [50] UP 1'-11 1/8 [587] | BFW 1 1 7 1/2" * [495] * MPT RAIN MPT RAIN | (4) 4° FLI | 2'-11 3/8" [-10 7/8" | SERIES FLOW PIPING /2" (SEE NOTE 7) AUX. CROSSOVER DRAIN (SEE NOTE 7) 1'-5 1/8" [435] | 11'-11 3/4" [3651] | 2 1/2 [64 - 24'-2" [7366] FACE A | | 1'-5 1/ | /8" }] |
| SHIPPING WEIGHT | 18540 lbs+ [84 | 10] kg+ | OPERATING WEIGHT | 25520 lbs+ [11580] kg+ | HEAVIEST SECTION 7370 lbs+ [| 3345] kg+ | NO. OF SHIPPING SECTIONS 4 | DRAWN BY: TAM | |