
DWG. # REV. UNIT **CLOSED CIRCUIT COOLER** CW4C141214-DRA-SF EVAPCO, INC. evapco DATE<sub>11/19/2025</sub> MODEL # SERIAL # NTS ATWB 14-7K12-Z NOTES: 1. (M)- FAN MOTOR LOCATION **FACE C** 2. HÉAVIEST SECTION IS FAN/CASING SECTION 3. MPT DENOTES MALE PIPE THREAD (2) ACCESS DOOR FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. \*-APPROXIMATE DIMENSIONS DO NOT USE **FACE B FACE D** FOR PRE-FABRICATION OF CONNECTING **PLAN VIEW** 7. SERIES FLOW PIPING AND AUX. CROSSOVER **DRAIN BY OTHERS** 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.




WEIGHT

40800 lbs+ [18510] kg+

29900 lbs+ [13565] kg+

WEIGHT

9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]



TAM