UNIT **CLOSED CIRCUIT COOLER** MODEL # ATWB 20-5L24-Z NTS


EVAPCO, INC. Evapco




DWG. # REV. WB36M2410-DRC-SF DATE_{11/14/2025} SERIAL #


NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE
- FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]



FACE A





SHIPPING 65700 lbs+ [29805] kg+ WEIGHT

OPERATING WEIGHT

101000 lbs+ [45815] kg+

HEAVIEST SECTION WEIGHT

13720 lbs+ [6225] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: