UNIT ED CIRCUIT CC	EVADOO T	NIC evapo	wg. # WV051214-DRD-ST	REV.
MODEL # LRWB 5-7M12 SCALE NTS	EVAPCO, I	NC.	ERIAL #	DATE 11/5/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT I [METRIC] [mn 6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIE 7. MAKE-UP WATER PRESSURE	DIAN VIEW	FACE C		FACE D
20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX		18'-2 5/8" 18'-2 553] FACE A		
2'-6 3/8" *				
4" [100] BFW FLUID IN		2" [15] PT VENT	[1905]	
4" [100] BFW FLUID OUT 3 1/4" TYP	6'-3/4" [1849] 9'-1" [2769]	ACCESS		6'-7 3/4" [2026]
[83]	3'-1/4" [919]	DOOR		1'-8 1/8" [511]
3" [80] MPT	2 5/8" 8 3/4" [67] [222] 7/8" 124] 1'-1 5/8" [346]	11'-5 3/4" [3499] 18'-2 5/8" [5553]	1" [25] MPT MAKE-UP	ACCESS DOOR
5-5/8" 5-5/8" FACE B		FACE A		
SHIPPING 190 lbs+ [4625] k	OPERATING)80 lbs+ [7295] F	HEAVIEST SECTION 90 lbs+ [4625] k	NO. OF SHIPPING SECTIONS	DRAWN BY: TLS