DWG. # REV. UNIT **CLOSED CIRCUIT COOLER** CW4C071208-DRA-ST EVAPCO, INC. evapco DATE_{10/28/2025} MODEL # SERIAL # NTS ATWB 7-4J12 NOTES: **FACE C** 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CASING SECTION (M)3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD ACCESS DOOR BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] **FACE B FACE D** 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING **PLAN VIEW** 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm] **FACE A** 1'-2" [356] 2'-11 3/8" [899] 1'-9 3/8" [543] 1'-10 7/8" [581] (2) 1/2" [15] FPT VENT 4'-8 3/8" [1432] (2) 4" [100] BFW FLUID IN 11'-11 5/8" [3648] 2'-3" [686] FLUID OUT (2) 4" [100] BFW 0 2" [50] MPT MAKE-UP 2" [50] MPT DRAIN 4'-3 7/8" [1318] 1'-11 1/8" [587] 1'-3" [381] 3" [80] MPT **OVERFLOW** 1'-5 1/8" [435] 11'-11 3/4" [3651] **FACE B FACE A** NO. OF SHIPPING SECTIONS DRAWN BY: **SHIPPING** OPERATING HEAVIEST SECTION

WEIGHT

8770 lbs+ [3980] kg+

TAM

14650 lbs+ [6650] kg+

10670 lbs+ [4840] kg+

WEIGHT

WEIGHT