UNIT CLOSED CIRCUIT COOLER		EVADOO T	NG evanço	DWG. # CW4C071812-DRA-ST REV	.
40DEL # ATWB 7-6J18	SCALE NTS	EVAPCO, I	NC. evapco	SERIAL # DATE <sub>12/14/</sub>	/2025
NOTES:  1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CA 3. MPT DENOTES MALE PIPE THE FPT DENOTES FEMALE PIPE THE FPT DENOTES BEVELED FOR GVD DENOTES GROOVED FLG DENOTES PLAINE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INC ACCESSORIES (SEE ACCESSO 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MA) 6. *-APPROXIMATE DIMENSIONS FOR PRE-FABRICATION OF CO PIPING 7. 3/4" [19mm] DIA. MOUNTING HO RECOMMENDED STEEL SUPPO 8. DIMENSIONS LISTED AS FOLLO ENGLISH FT-IN METRIC [mm]	READ HREAD WELDING  LUDE RY DRAWINGS)  [344 kPa] DO NOT USE NNECTING  DLES. REFER TO DRT DRAWING.	PLAN	FACE B /IEW	FACE C  ACCESS DOOR  FACE A	E D
2" [50] MPT (2) 4* [100] BFW  2" [50] MPT DRAIN  1'-11 1/8" [587] 3" 51/4" [107] 5'-3.5 [161]	6 1/4" *	2'-11 3/8" [899]  1'-10 7/8" *  5'-11 3/8" [1813]  13'-11" [4242]	[356] (2) 1/2" [15] FPT VENT  47/8"	18'-0" [5486]	
SHIPPING 20630 lbs+		OPERATING 28150 lbs+ [12770] kg+	HEAVIEST SECTION WEIGHT 17610 lbs+ [7990] kg+	NO OF CHIPDING SECTIONS DRAWN BY:	AM