UNIT CLOSED CIRCUIT COOLED				•	DWG. #	W2/000040 DDF CF	REV.	
MODEL #	CLOSED CIRCUIT CO	CCALE	EVAPC	O. INC.	evapco	SERIAL #	WV080910-DRE-SF	-
HODEL #	LRWB 8-5L9-Z	SCALE NTS				SLIVIAL #		DATE 11/4/2025
2. MPT FPT I BFW GVD FLG PE D 3. +UNI ACCI 4. 3/4" [RECC 5. DIME 6. * - AF USE CONI 7. MAKI 20 ps 8. SERI	FAN MOTOR LOCATION DENOTES MALE PIPE THREADENOTES FEMALE PIPE THREADENOTES BEVELED FOR WIDDENOTES FLANGE DENOTES FLANGE DENOTES PLAIN END IT WEIGHT DOES NOT INCLUESSORIES (SEE ACCESSOR) [19mm] DIA. MOUNTING HOLE OMMENDED STEEL SUPPOR ENSIONS LISTED AS FOLLOW PPROXIMATE DIMENSIONS D FOR PRE-FABRICATION OF INECTING PIPING. E-UP WATER PRESSURE SIE [137 KPa] MIN, 50 psi [344 KF IES FLOW PIPING AND AUX. (1) IN ARE BY OTHERS	READ /ELDING JDE Y DRAWINGS) ES. REFER TO RT DRAWING VS: ENGLISH FT IN [METRIC] [mm] DO NOT	FACE PLAN VIE	1 2000 3		CE C		<u>FACE D</u>
2 [2'-1/2" * - 3'-8	8 7/8" * - 				15'-2 1/4" [4629] CE A		
(2) 4" [[100] BFW O		5'-2 1/4"		(2) 1/2" [15] FPT VENT SERIES FLOW PIPING	-	[1905]	
	" [100] BFW FLUID OUT		2'-10 1/2" * [1583] [876] * 8'-2 1 [250	/2" 2]	(BY OTHERS) AUX. CROSSOVER DRAIN (BY OTHERS)	72		6'-7 3/4" [2026]
	[80] MPT	Mo-	7" * 3'-1/4" [919] 2 5/8"		ACCESS DOOR 8'-5 3/8" [2575]		1'-8 1/8" [511]	ACCESS
	[80] MPT /ERFLOW	4 1/4" [108]	L 222 J				2" [50] MPT MAKE-UP	DOOR
2"	[50] MPT 7'	2'-10" [864] 2388]	-	1'-3 7/8" [405]		15'-2 1/4" [4629]	-	
		CE B			<u>FA</u> (CE A		