JNIT	CLOSED CIRCUIT COOLER		EVAPCO, INC. evapco			DWG. # CW4C071812-DRA-SF	REV.
IODEL #	ATWB 7-6J18-Z	SCALE NTS	EVAP	O, INC.		SERIAL #	DATE _{12/14/2025}
2. HÉAVI 3. MPT D FPT DI BFW D GVD D FLG DI PE DE 4. +UNIT ACCES 5. MAKE- 20 psi 6. *-APPF FOR P PIPING 7. SERIE DRAIN 8. 3/4" [19 RECOI 9. DIMEN E	AN MOTOR LOCATION EST SECTION IS FAN/CASI ENOTES MALE PIPE THRE ENOTES FEMALE PIPE THRE ENOTES BEVELED FOR W ENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLU SSORIES (SEE ACCESSOR' UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [3 ROXIMATE DIMENSIONS DO RE-FABRICATION OF CONIC S FLOW PIPING AND AUX. (6 BY OTHERS. DMM] DIA. MOUNTING HOLE MIMENDED STEEL SUPPOR SIONS LISTED AS FOLLOW NGLISH FT-IN IETRIC [mm]	AD READ ELDING JDE Y DRAWINGS) JA4 kPa] D NOT USE NECTING CROSSOVER ES. REFER TO T DRAWING.		FACE B	ACCESS	FACE C ACCESS FACE A	DOOR = =:
2" [50] MAH 2" [50] C 	00] BFW 00] BFW 1067 1 10	(4)	2'-11 3/8" [899] 1'-10 7/8" * 5'-11 3/8" [1813] 4" [100] BFW FLUID OUT 13'-11" [4242] - 5 1/4" * [1530] 1-3" 181]	SERIES FLOW PIPING (SEE NOTE 7) AUX. CROSSOVER DRAIN (SEE NOTE 7)			
	4 1/4" 4 1/4" [107] 5'-3 5/8' [1616] 7 [22	" 4" 35 1	- 3" [80] MPT OVERFLOW	1'-4 7/8" [429]		18'-0" [5486]	

FACE B

FACE A