UNIT	CLOSED CIRCUIT COOLER	
MODEL #	LRWB 8-5N12-Z	SCALE NTS

EVAPCO, INC. Evapeo

DWG. # WV081210-DRE-SF REV. SERIAL # DATE 11/3/2025

NO. OF SHIPPING SECTIONS

DRAWN BY:

## NOTES:

**SHIPPING** 

WEIGHT


- 1. (M)- FAN MOTOR LOCATION
- 2. MPT DENOTES MALE PIPE THREAD
  FPT DENOTES FEMALE PIPE THREAD
  BFW DENOTES BEVELED FOR WELDING
  GVD DENOTES GROOVED
  FLG DENOTES FLANGE
  PE DENOTES PLAIN END
- 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
- 6. \* APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.
- 7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX
- 8. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS


**OPERATING** 

WEIGHT

11960 lbs+ [5425] kg+

19350 lbs+ [8780] kg+





HEAVIEST SECTION

WEIGHT

11960 lbs+ [5425] kg+