UNIT CLOSED CIRCUIT COOLER	EVADOO TI	NC evapco	DWG. # WV050604-DRC-ST	REV.
MODEL # LRWB 5-2H6 SCALE NTS	EVAPCO, II	YC.	SERIAL #	DATE 11/4/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT [METRIC] [mr 6. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PI 7. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX	FACE B [1540]	FACE C		FACE D
2'-6 3/8" * [770] * 4" [100] BFW FLUID IN 4" [100] BFW FLUID OUT 3 1/4" TYP. 3" [80] MPT OVERFLOW	3'-7 1/2" [305] * [1106] 6'-7 3/4" [2026] 1'-3/4" * [324] * 3'-1/4" [919] 1 8 3/4" [222]		[1905]	6'-7 3/4" [2026] -8 1/8" [511]
2" [50] MPT	- 4 7/8" [124] - 1'-1 5/8" [346]	12'-2 7/ [3731 FACE A		- ACCESS DOOR
SHIPPING 3340 lbs+ [1515] kg+ WEIGHT	OPERATING	HEAVIEST SECTION 3340 lbs+ [1515] kg+	NO. OF SHIPPING SECTIONS 1	RAWN BY: TLS