UNIT	CLOSED CIRCUIT COOLER	
MODEL #	LSWE 10-3M12-Z	SCALE NTS


EVAPCO, INC. Evapeo

DWG. # REV. WLETM1206-DRD-SF DATE_{12/14/2025} SERIAL #

NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED**
 - FLG DENOTES FLANGE PE DENOTES PLAIN END
- 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC1 [mm]
- 6. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. HEAVIEST SECTION IS COIL SECTION
- 8. MAKE-UP WATER PRESSURE
- 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX 9. SERIES FLOW PIPING AND AUX. CROSSOVER
- DRAIN ARE BY OTHERS


FACE C



FACE D







SHIPPING 12770 lbs+ [5795] kg+ WEIGHT

OPERATING WEIGHT

19240 lbs+ [8730] kg+

HEAVIEST SECTION WEIGHT

7880 lbs+ [3575] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: