UNIT CLOSED CIRCUIT COOLER			EV	ADCO T	NC ev	evapco		DWG. # WV050906-DRC-ST		REV
MODEL #	eco-LRWB 5-3K9	SCALE NTS	T EV	APCO, I	NC.		SERIAL #			DATE _{11/26/2025}
2. MPT DEN FPT DEN BFW DE GVD DEN FLG DEN PE DEN(3. +UNIT W ACCESS 4. 3/4" [19m RECOMM 5. DIMENSI 6. * - APPR USE FOF 7. MAKE-UI	MOTOR LOCATION NOTES MALE PIPE THREA IOTES FEMALE PIPE THREA NOTES BEVELED FOR WANTES FLANGE DITES PLAIN END EIGHT DOES NOT INCLU ORIES (SEE ACCESSOR) IMP DIA. MOUNTING HOLE MENDED STEEL SUPPOR ONS LISTED AS FOLLOW OXIMATE DIMENSIONS DA R PRE-FABRICATION OF OP WATER PRESSURE BY KPA] MIN, 50 psi [344 KF	READ ELDING DE (DRAWINGS) ES. REFER TO T DRAWING (/S: ENGLISH FT [METRIC] [mi O NOT CONNECTING PI	m] <u>FACE</u>	1 = 1		FACE C			(প)	FACE D
	_ - 2'-6 3/8" ∗ -				7//	15'-2 1/4' [4629] FACE A	·	6'-3" [1905]	-	4
4" [100] E FLUI 4" [100] E FLUID G 3 1/4" T [83] T OVERFL	APT OW		3'-7 1/2" -7 1/2" * [1106] 495] * [20] 5 1/4" * [919] 2 5/8" 8 3/4" [67] 8 3/4" [47/8" [124]	3/4" 226]		CCESS DOOR 8'-5 3/8" [2575]	1" [25] MPT (E-UP	4.0	6'-7 3/4" [2026] 1'-8 1/8" [511] ACCESS DOOR
2" [50] I DR	FACE I	1'-8 7/8" 530	ODEDATING	1'-1 5/8" [346]	HEAVIEST SECTION	15'-2 1/4' [4629] FACE A		SHIPPING SECTIONS	IDR/	AWN BY: TLS
WEIGHT	5890 lbs+ [267	5] kg+	WEIGHT 92	80 lbs+ [4210] kg+	WEIGHT	5890 lbs+ [2675] kg+		1		TLS