

UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-LRWB 5-5J9	SCALE NTS

NOTES:

- (M)- FAN MOTOR LOCATION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING
- DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN
[METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING
- MAKE-UP WATER PRESSURE
20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX


PLAN VIEW

FACE B

5'-5 1/8" [1540]

FACE C

FACE D



1'-1 5/8" [346]

15'-2 1/4" [4629]

1" [25] MPT MAKE-UP

1'-8 1/8" [511]

ACCESS DOOR

6'-3" [1905]

6'-7 3/4" [2026]

ACCESS DOOR

8'-5 3/8" [2575]

15'-2 1/4" [4629]

FACE A

