

| | |
|---------|-----------------------|
| UNIT | CLOSED CIRCUIT COOLER |
| MODEL # | eco-LRWB 3-3E6-Z |

EVAPCO, INC. 

| | | | |
|----------|-----------------|------|-----------|
| DWG. # | WV030606-DRD-SF | REV. | - |
| SERIAL # | | DATE | 1/31/2026 |

NOTES:

1. (M)- FAN MOTOR LOCATION
2. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING
5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN
[METRIC] [mm]
6. * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF
CONNECTING PIPING.
7. MAKE-UP WATER PRESSURE
20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX
8. SERIES FLOW PIPING AND AUX. CROSSOVER
DRAIN ARE BY OTHERS

