


| | |
|---------|-----------------------|
| UNIT | CLOSED CIRCUIT COOLER |
| MODEL # | eco-LRWB 8-3M9-Z |

| | | | |
|----------|-----------------|------|-----------|
| DWG. # | WV080906-DRE-SF | REV. | - |
| SERIAL # | | DATE | 1/31/2026 |


NOTES:

1. (M)- FAN MOTOR LOCATION
2. MPT DENOTES MALE PIPE THREAD
3. FPT DENOTES FEMALE PIPE THREAD
4. BFW DENOTES BEVELED FOR WELDING
5. GVD DENOTES GROOVED
6. FLG DENOTES FLANGE
7. PE DENOTES PLAIN END
8. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
9. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
10. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
11. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.
12. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX
13. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS

PLAN VIEW



FACE B



FACE A