UNIT CLOSED CIRCUIT COOLER			E\/AI			/apco	DWG. #	WLE040906-DRD-S7	T	EV
MODEL #	eco-LSWE 4-3H9	SCALE NTS	EVA	PCO, II	VC.		SERIAL #		D	ATE _{11/27/2025}
2. HÉAVII 3. MPT D FPT DE BFW D GVD D FLG DE PE DEI 4. +UNIT ACCES 5. 3/4" [18 RECON 6. DIMEN 7. * - APP USE FC 8. MAKE- 20 psi [9. MAKE-	AN MOTOR LOCATION EST SECTION IS COIL SECTIO ENOTES MALE PIPE THREAD ENOTES BEVELED FOR WELE ENOTES GROOVED ENOTES FLANGE NOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUDE SSORIES (SEE ACCESSORY D DMM] DIA. MOUNTING HOLES. MMENDED STEEL SUPPORT D SIONS LISTED AS FOLLOWS: PROXIMATE DIMENSIONS DO N OR PRE-FABRICATION OF COI UP WATER PRESSURE [137 kPa] MIN, 50 psi [344 kPa] UP CONNECTION END OF UNIT	ND DING RAWINGS) REFER TO PRAWING ENGLISH FT IN [METRIC] [mm] NOT NNECTING PIPI MAX 1-5/8" [194]		FACE DE PLAN VIEW	-	FAC	"-11 1/4" ——		<u>FACE</u>	<u>D</u>
	4" [100] BFW FLUID IN 4" [100] BFW FLUID OUT (2) ACCESS DOOR — 1" [25] MPT MAKE-UP 2'-2 1/8" [664] 1'-7 5/8" [498]		1'-7 1/2" *		7'-5 1/2" [2273]	1/2" [15] FPT VENT 8' [FACI	-11 1/4" 2724]			
SHIPPING WEIGHT	4390 lbs+ [1995]] kg+	OPERATING 5970 lbs	+ [2710] kg+	HEAVIEST SECTION WEIGHT	2850 lbs+ [1295] kg+	NO. OF	SHIPPING SECTIONS 2	DRAW	'N BY: TLS