

UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-LSWE 8P-5N18	SCALE NTS

EVAPCO, INC.

DWG. #	WLEP81810-DRD-ST	REV.	-
SERIAL #		DATE	2/1/2026


NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
CVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING
6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN
[METRIC] [mm]
7. * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING
8. MAKE-UP WATER PRESSURE
20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX


FACE B **PLAN VIEW**

FACE C


FACE D



FACE A



FACE A



FACE B

SHIPPING WEIGHT 22630 lbs+ [10265] kg+ OPERATING WEIGHT 31790 lbs+ [14420] kg+ HEAVIEST SECTION WEIGHT 17230 lbs+ [7820] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: TLS