

UNIT	CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. #	WLETM2412-DRD-ST	REV.
MODEL #	eco-LSWE 10-6M24	SCALE NTS		SERIAL #		DATE 2/1/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING
6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN
[METRIC] [mm]
7. * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING
8. MAKE-UP WATER PRESSURE
20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX




DWG. # WLETM3413.DBD ST

REV.


SERIAL #

DATE 2/1/2026

FACE C



FACE B **PLAN VIEW**



SHIPPING WEIGHT 44860 lbs+ [20350] kg+ OPERATING WEIGHT 61900 lbs+ [28080] kg+ HEAVIEST SECTION WEIGHT 17830 lbs+ [8090] kg+ NO. OF SHIPPING SECTIONS 3 DRAWN BY: TLS