UNIT CLOSED CIRCUIT COOLER

MODEL # eco-LSWE 10-4L18 SCALE NTS

EVAPCO, INC. Evapeo


DWG. # WLETM1808-DRD-ST REV.
SERIAL # DATE 11/26/2025

FACE D

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS COIL SECTION
- 3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE
- ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TÓ RECOMMENDED STEEL SUPPORT DRAWING
- 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN
 - [METRIC] [mm]
- 7. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 8. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX

FACE C



4'-9" [1448] 2'-6 3/8" * - (2) 4" [100] BFW FLUID IN (2) 1/2" [15] 4'-9 5/8" [1464] **FPT VENT** 2'-6 3/4" * (2) 4" [100] BFW **FLUID OUT** 0 13'-4 1/8" [4067] (2) ACCESS DOOR -2" [50] MPT MAKE-UP 8'-6 1/2" [2604] 3" [80] FPT **OVERFLOW** 2'-7 1/2" \[800 \] 2'-1/8" 2'-7 3/4" 2'-1" [635] 18'-1/4" [5493] 3" [80] MPT 3'-7 1/4" [1099] DRAIN **FACE A** 4'-1 7/8" [1267]

SHIPPING WEIGHT

25900 lbs+ [11750] kg+

FACE B

OPERATING WEIGHT

36640 lbs+ [16620] kg+

HEAVIEST SECTION WEIGHT

18710 lbs+ [8490] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: