UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-LSWE 10-5L18	SCALE NTS

EVAPCO, INC. Evapeo

DWG. # REV. WLETM1810-DRD-ST DATE_{11/26/2025} SERIAL #

FACE D

DRAWN BY:


NO. OF SHIPPING SECTIONS

SHIPPING


WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS COIL SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
- 7. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 8. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX

FACE C



FACE A



41410 lbs+ [18785] kg+

HEAVIEST SECTION

WEIGHT

22480 lbs+ [10200] kg+

OPERATING

WEIGHT

29670 lbs+ [13460] kg+