JNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-I SWF 4-2F6-7	SCALE NITS


EVAPCO, INC. Evapeo

DWG. # WLE040604-DRE-SF REV. SERIAL # DATE\_11/27/2025


## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END
- 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TÓ RECOMMENDED STEEL SUPPORT DRAWING
- 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
- 6. \* APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.
- 7. MAKE-UP WATER PRESSURE
- 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX 8. MAKE-UP CONNECTION LOCATED 7-5/8" [194] FROM CONNECTION END OF UNIT
- 9. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS

## **FACE C**



FACE D





SHIPPING WEIGHT 2630 lbs+ [1195] kg+

OPERATING WEIGHT

3560 lbs+ [1615] kg+

HEAVIEST SECTION WEIGHT 1500 lbs+ [685] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: