INIT	CLOSED CIRCUIT COOLER	
IODEL #	eco-I SWF 4-5I6-7	SCALE NTS



DWG. # WLE040610-DRD-SF REV. SERIAL # DATE_11/27/2025


FACE D

DRAWN BY:


NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END
- 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TÓ RECOMMENDED STEEL SUPPORT DRAWING
- 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
- 6. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. HEAVIEST SECTION IS COIL SECTION
- 8. MAKE-UP WATER PRESSURE
- 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX
- 9. MAKE-UP CONNECTION LOCATED 7-5/8" [194] FROM CONNECTION END OF UNIT
- 10. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN ARE BY OTHERS

FACE C



FACE A





SHIPPING WEIGHT 4150 lbs+ [1885] kg+ OPERATING WEIGHT 5420 lbs+ [2460] kg+ HEAVIEST SECTION WEIGHT 2940 lbs+ [1335] kg+ NO. OF SHIPPING SECTIONS