UNIT	CLOSED CIRCUIT CO	OOLER		EVADOO THE			DWG. # WLEP81210-DRE-SF		REV.
MODEL #	eco-LSWE 8P-5O12-Z	SCALE NTS	E	EVAPCO,		INC. Evapeo		SERIAL #	
2. MPT I FPT I BFW GVD FLG I PE DI 3. +UNI ⁻ ACCE 4. 3/4" [I RECC 5. DIME 6. * - AP USE I 7. HEAV 8. MAKE 20 ps 9. SERII	FAN MOTOR LOCATION DENOTES MALE PIPE THRE DENOTES FEMALE PIPE THRE DENOTES BEVELED FOR W DENOTES GROOVED DENOTES FLANGE ENOTES PLAIN END I WEIGHT DOES NOT INCLU- ESSORIES (SEE ACCESSOR' 19mm] DIA. MOUNTING HOLI- DIMMENDED STEEL SUPPOR NSIONS LISTED AS FOLLOW PROXIMATE DIMENSIONS DE- FOR PRE-FABRICATION OF INCLU- I TEST SECTION IS COIL SEC- E-UP WATER PRESSURE I [137 KPa] MIN, 50 psi [344 KF ES FLOW PIPING AND AUX. IN ARE BY OTHERS	READ FELDING JDE Y DRAWINGS) ES. REFER TO RT DRAWING VS: ENGLISH FT IN [METRIC] [mm] DO NOT CONNECTING PIPING TION Pa] MAX			FACE PLAN VIE		FACE C		FACE D
	2'-1/: [624 SERIES FLOW ——	2" *	-	3'-8 7/8" * [1140]			FACE A		
	PIPING (BY OTHERS)			(2) 4" [100] BFW FLUID IN		(2) FP1	1/2" [15] Γ VENT		
2	'-10 1/2" * [876]				5'-1 1/4" [1556]		AUX. CROSSOVER DRAIN (BY OTHERS)		
	7 1/8" * (2) ACCESS I	DOOR		(2) 4" [100] BFW FLUID OUT		12'-4 5/8"	M		
	3" [80] N OVERFL			2" [50] MPT MAKE-UP	7'-3 3/8" [2219]				

